



## Continuous-Wave Laser Source for High Speed Spectroscopy

[View U.S. Patent No. 7,483,143 in PDF format.](#)

**WARF: P06122US**

Inventors: Scott Sanders, Joachim Walewski

**The Wisconsin Alumni Research Foundation (WARF) is seeking commercial partners interested in developing a simple and inexpensive laser-based spectroscopy approach.**

### Overview

Measurements of emission and absorption spectra provide a valuable means of identifying and analyzing gases, liquids and solids. Fourier transform infrared (FTIR) and grating spectrometers are two common commercial tools for measuring spectra; however, both have drawbacks. Because they employ moving mirrors, FTIRs are relatively slow, with a time resolution of tens of milliseconds. Grating spectrometers rely on sophisticated and application-specific cameras, and their light throughput is low, limiting their usefulness for high resolution spectral analysis. In addition, both methods use incoherent, low-radiance light sources.

### The Invention

UW-Madison researchers have devised a simple and inexpensive laser-based spectroscopy approach that is similar to FTIR in principle; however, because it has no moving parts, it offers many advantages, including the ability to produce spectra every microsecond or faster. The laser is generally fashioned as a fiber laser, which is a laser cavity composed primarily of fiber optic cable. To measure spectra, the continuous-wave fiber output is directed at the test article and onto a single photoreceiver. The photoreceiver signal is then digitally processed to produce the desired spectra.

### Applications

- Suitable for any application where high speed sensing of spectra is needed, including high speed gas sensing in engines and medical imaging (e.g., optical coherence tomography)

### Key Benefits

- Simple and inexpensive to manufacture: Requires no camera or moving parts
- Potentially 10 times less expensive to make than an FTIR spectrometer
- Much faster than traditional FTIR spectroscopy, with a time resolution in the range of 0.1 to 10,000 microseconds
- Capable of high spectral resolution with high signal-to-noise ratios
- Extremely flexible: Can be configured for low or high resolution spectral analysis by simply adjusting the digital processing parameters
- Replaces the lamp found in traditional spectrometers with a low cost continuous-wave laser—a light source that is brighter, more efficient, and compatible with fiber optics

We use cookies on this site to enhance your experience and improve our marketing efforts. By continuing to browse without changing your browser settings to block or delete cookies, you agree to the storing of cookies and related technologies on your device. [See our privacy policy.](#)

Additional Information

OK



**WARF**  
Wisconsin Alumni Research Foundation

| [info@warf.org](mailto:info@warf.org) | 608.960.9850

#### For More Information About the Inventors

- [Scott Sanders](#)

#### Tech Fields

- [Analytical Instrumentation, Methods & Materials : General analytical instrumentation](#)
- [Analytical Instrumentation, Methods & Materials : Lasers](#)
- [Analytical Instrumentation, Methods & Materials : Spectroscopy](#)
- [Medical Imaging : Other diagnostic imaging](#)

For current licensing status, please contact Michael Carey at [mcarey@warf.org](mailto:mcarey@warf.org) or 608-960-9867

We use cookies on this site to enhance your experience and improve our marketing efforts. By continuing to browse without changing your browser settings to block or delete cookies, you agree to the storing of cookies and related technologies on your device. [See our privacy policy.](#)

OK



**WARF**  
Wisconsin Alumni Research Foundation

| [info@warf.org](mailto:info@warf.org) | 608.960.9850