

Robust and Improved Surfaces for Biological Microarrays That Reduce Nonspecific Binding

View U.S. Patent No. 9,051,667 in PDF format.

WARF: P07188US

Inventors: Padma Gopalan

The Wisconsin Alumni Research Foundation (WARF) is seeking commercial partners interested in developing improved surfaces for microarrays.

Overview

Biological microarrays are valuable tools that enable the parallel analysis of thousands of different analytes. However, one of the chief problems with existing protein microarrays is the nonspecific binding of target molecules on the array. This creates background noise and makes it difficult to detect the specific binding of the target at probe locations.

Polymer films provide an alternative substrate for microarrays. However, these films lack stability in most mediums. Coating the substrate with epoxide-containing polymers is another option, but most of these polymers form uncrosslinked films with poor stability and a tendency to delaminate.

The Invention

A UW-Madison researcher has developed a robust coating for use in microarrays. This reactive polymer coating has a high mechanical stability, binding-site density and signal-to-noise ratio. It can be formed readily on many substrates and may also be patterned to control the localization and density of the target molecules.

The coating consists of a cross-linked epoxy-functional copolymer film. The copolymers incorporate at least two sets of polymerized monomers. The first set, which contains epoxide groups, reacts with the target molecules to immobilize them on the film. The second set contains photo-cross-linkable groups, which are used to cross-link the copolymers into a stable film. Using different monomers to provide the cross-linking and target binding functions allows each function to be controlled and optimized independently.

Applications


Improved surfaces for biological microarrays

Key Benefits

- Significantly reduces nonspecific binding
- Signal-to-noise ratio is three to six times higher than commercially available 2-D arrays of epoxy groups.
- The photo-cross-linking mechanism creates a robust reactive coating that does not peel or delaminate for months in aqueous or

We use coorder in mostle to enhance your experience and improve our marketing efforts. By continuing to browse without changing your browser settings to block or delete

- Substrate-independentichemistry-allowsstuirfacectolies created ontglassystiticon/wafersyst8inlessesteely.gdls).or polycarbonate.
- Easy chemical tunability enables incorporation of other desirable features, such as a non-fouling surface or multiple target binding.



- · Can be photo-patterned by exposure to UV light
- · Does not require plasma deposition or processing
- · Can be combined easily with ultrasonic plotting or an ultrasonic sprayer for scalability

Stage of Development

The development of this technology was supported by WARF Accelerator. WARF Accelerator selects WARF's most commercially promising technologies and provides expert assistance and funding to enable achievement of commercially significant milestones. WARF believes that these technologies are especially attractive opportunities for licensing.

Additional Information

For More Information About the Inventors

• Padma Gopalan

Related Intellectual Property

• View Continuation Patent in PDF format.

Publications

• Cullen S.P., Ha S., Lagally M.G. and Gopalan P. 2008. Photopatternable Substrate-independent Poly (glycidyl methacrylate-ran-2-(acryloyloxy) ethyl 2-methylacrylate) Polymer Films for Immobilization of Biomolecules. J. Polymer Sci. Part A 46, 5826-5838.

Tech Fields

Engineering : Micro & nanotechnologies

For current licensing status, please contact Jennifer Gottwald at jennifer@warf.org or 608-960-9854

We use cookies on this site to enhance your experience and improve our marketing efforts. By continuing to browse without changing your browser settings to block or delete cookies, you agree to the storing of cookies and related technologies on your device. See our privacy policy

